

## Product information

# 82 02 200

## KNIPEX TwinGrip Slip Joint Pliers



- Unique combination: Front grip and side grip function, box joint, push button adjustment
- Very slim pliers let you work even in confined installation spaces with a narrow turning zone for fast results
- High-grip front jaw with robust teeth and high gear ratio at the tip of the mouth
- Large front and side gripping capacity for diameters and widths across flats 4 - 22 mm
- Reliable front gripping of flat workpieces due to the three-point system
- Gripping, tightening and loosening screws with worn heads and threads
- Five-way adjustable slip joint with push button adjustment for precise adjustment of gripping capacity
- Pinch stop reduces the risk of crushed fingers
- Durable and resilient due to the robust box joint
- Forged from high-grade chrome vanadium electric steel, oil-hardened, teeth additionally induction-hardened to approx. 61 HRC

### General

Article No.	82 02 200
EAN	4003773087250
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	280 g
Dimensions	200 x 51 x 22 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Adjustment positions	5
Capacities for pipes (diameter)	Ø 5/32 – 7/8 Inch
Capacities for pipes (diameter)	Ø 4 – 22 mm
Capacities for nuts	4 – 22 mm
Capacities for nuts	5/32 – 7/8 Inch

*technical change and errors excepted*



