



DBK 1X4



Approvals



General Data

Type	DBK 1X4
Wire Termination Technology	Screw Clamp
Ratings	800 V/IC-114 A,OG-57 A/IC-35 sq mm,OG-10 sq mm/IC-6 Nm,OG-1.2 Nm
GTIN / Harmonize Custom Code	85389000
Standard Packing Qty (in No)	10
Country of Origin	India
Screw Size	M4

Dimensions & Weight

Height (mm)	49.70
Height (inches)	1.96
Width (mm)	67.50
Width (inches)	2.66
Thickness (mm)	73
Weight For Standard Packing Qty (Kg)	1.47

Material Data

Housing	PA 6,6
Standard Colour	Grey
Other Color Variants	Black, Blue, Green, Khakhi, Red, Yellow

Rated Conductor Size

Stranded Wire - min (sq mm)	IC-10, OG-2.5
Stranded Wire - max (sq mm)	IC-50, OG-10
Solid Wire - min (sq mm)	IC-10, OG-2.5
Solid Wire - max (sq mm)	IC-50, OG-16

Ratings - IEC

Standard	IEC 60947-7-1
Rated Voltage (V)	800
Rated Current (A)	IC-114, OG-57
Rated Cross Section (sq mm)	IC-35, OG-10
Short Time Withstand Current (kA)	4.20
Rated Impulse Withstand Voltage(kV)	-
Pollution Degree	III

Ratings-uL

Rated Voltage (V)	600
Rated Current (A)	IC-130, OG-130
Conductor Size - min (AWG)	IC-8, OG-16
Conductor Size - max (AWG)	IC-1, OG-6

Accessories

Partition Plate Without Foot

KBX

Height : 43 mm

Width : 54 mm

Thickness : 1.50 mm



Partition Plate With Foot


End Clamp

SCUDD

Height : 50 mm

Width : 55.50 mm

Thickness : 10 mm




SCUSL

Height : 41 mm


Width : 47.50 mm

Thickness : 8 mm



Marking Label

LABEL KN10



Mounting Channel (Standard Lengths 300 mm, 500 mm, 1000 mm)

Elmex Elmex Elmex Elmex Elmex Elmex Elmex Elmex Elmex Elmex Elmex

