


## Click Square Diffusers

Cover E9 click 2m opal

0022630



### Product features

- A click diffuser made of acrylic thermoplastic (PP). Operating temperature: -15 - 85 [°C]. IK rating: 08. UV resistant. Fire hazard certificate according to IEC 60695-2-11. Compatible with the following profiles: Profile deep wide surface 30 CDE-9/T (0022599), Profile shallow wide surface 30 CDE-9/T (0022600). Transparency level 70%.



## PRODUCT OVERVIEW

Product name	Cover E9 click 2m opal
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278043
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226309

## DATA TABLE

### General data

Product name	Cover E9 click 2m opal
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278043
Warranty	3 years

### Physical data

Housing colour	Silver
Diffuser finish	Opal
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	33.4
Nominal Product Height (mm)	26.3
Weight (kg)	0.02

### Packaging

Single packaging type	Carton
Product EAN number	5410288226309

## Click Square Diffusers

Cover E9 click 2m opal

0022630

Packaging single length / height (cm)	200.0
Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288226309
Units per outer package	20
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

### TECHNICAL DRAWINGS

