

## PTGN clamp holder, right

For copy turning and longitudinal turning using TN indexable insert

**ATORN**<sup>®</sup>

### Application


For copy turning and longitudinal turning using TN indexable insert 60°

### Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type T, 90° pitch angle, 60° tip angle, 0° clearance angle

### Advantage

- three-edge geometry lowers costs per cut
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



<b>Art. No.</b>	<b>17839 031</b>
<b>ISO name</b>	PTGN R/L 2525 M16
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	22 mm
<b>Programming size</b>	32 mm
<b>Suitable for indexable inserts</b>	TN.. 1604..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293126877