

### **CR2477N** 3V Lithium Battery


Swiss Made


# **Technical Data Sheet**

## **Specifications**


Li / MnO <sub>2</sub>
3 V
950 mAh
1.0 mA
2.5 mA
~ 8.3 g
-40 - +85 °C
< 1% / year

#### Performance







#### Dimensions



Discharge performance at 23°C





<sup>\*</sup>In applications where the battery is exposed to temperatures above 70 °C, please contact Renata for consultancy. \*\* The maximum current is determined for a yield of 70% of the nominal capacity with a cut-off voltage of 2.0V, at 23°C.

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the ASDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage <a href="https://www.renata.com/downloads/restriction">www.renata.com/downloads/restriction of use</a>

Rev. CR2477N.08 / 08.2019

Renata SA CH-4452 Itingen/Switzerland Tel. +41 (0)61 975 75 75 Fax. +41 (0)61 975 75 95 sales@renata.com www.renata.com A COMPANY OF THE SWATCH GROUP