

Communication Module



SMART AND FLEXIBLE

- WLAN or Ethernet, flexible compatibility of plant networking, one-click access to iSolarCloud
- Automatic network configuration with DHCP, transmission without configuration
- Free WLAN configuration, easy and time saving

SIMPLE AND EFFICIENT

- Plug and play, quick installation
- Data interval in seconds, quick glance for what you want
- Support of Smart IV Curve Diagnosis*
- Support of local and remote parameter setting and firmware updates

SAFE AND RELIABLE

- Password and encrypted transmission for data protection
- IP66, wide temperature range

Type designation	WiNet-S
Communication	
Max. number of supported devices	1
LED display	LED × 3
Communication Mode	
Internet communication	Channel x 1, 10/100Mbps self-adaption, Communication distance ≤100m
WLAN communication	802.11 b/g IEEE802.11n HT20@2.4GHz IEEE802.11n HT40@2.4GHz 2.4 GHz
Power supply	
DC input	5 VDC, 2.1 A
Power consumption	≤5 W
Ambient conditions	
Operating temperature	-30 °C to 60 °C
Relative air humidity	≤95 % (non-condensing)
Elevation	≤4000 m
Protection class	IP66
Mechanical parameters	
Dimensions (W * H * D)	48 mm * 132 mm * 36 mm
Mounting type	Plug and Play

*: WiNet-S is part of Smart IV Curve Diagnosis solution

