





### MAT Range of Stainless Steel Cable Ties

#### Features and Benefits

The MAT ties are similar in design to conventional 'plastic' cable ties and work on a ratchet system. Available in type 316 stainless steel.



Stainless Steel Cable Ties can be used at temperatures up to 538° C.



MAT

**Material specification please see page 83.**

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Application Tool
MAT Uncoated							
111-92080	<b>MAT8SS7</b>	230	7.0	60.0	445	SS316	MTT6
111-92120	<b>MAT12SS7</b>	330	7.0	90.0	445	SS316	MTT6
111-92160	<b>MAT16SS7</b>	430	7.0	120	445	SS316	MTT6
111-92240	<b>MAT24SS7</b>	630	7.0	180	445	SS316	MTT6
111-93080	<b>MAT8SS12</b>	230	12.0	60.0	445	SS316	MTT6
111-93120	<b>MAT12SS12</b>	330	12.0	90.0	445	SS316	MTT6
111-93160	<b>MAT16SS12</b>	430	12.0	120	445	SS316	MTT6
111-93240	<b>MAT24SS12</b>	630	12.0	180	445	SS316	MTT6
MAT Fully Coated							
111-92004	<b>MAT8SSC7</b>	230	7.0	60.0	445	SS316, SP	MTT6
111-96120	<b>MAT12SSC7</b>	330	7.0	90.0	445	SS316, SP	MTT6
111-92162	<b>MAT16SSC7</b>	430	7.0	120	445	SS316, SP	MTT6
111-92200	<b>MAT24SSC7</b>	630	7.0	180	445	SS316, SP	MTT6
111-92002	<b>MAT8SSC12</b>	230	12.0	60.0	445	SS316, SP	MTT6
111-92122	<b>MAT12SSC12</b>	330	12.0	90.0	445	SS316, SP	MTT6
111-92163	<b>MAT16SSC12</b>	430	12.0	120	445	SS316, SP	MTT6
111-92201	<b>MAT24SSC12</b>	630	12.0	180	445	SS316, SP	MTT6

All dimensions in mm. Subject to technical changes.



Please Note for Product Specific Approvals please refer to the Appendix