


# 13103-016 PSU 19" DC/DC COOLPOWER 100 W, TRIPLE, CPDC 312





# **KEY FEATURES**

Wide input voltage range from 20 to 72-VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

# **PRODUCT ATTRIBUTES**

Product Type: Power Supply

Type: 19" DC/DC Converter

Input Voltage DC: 20 - 72 V

Power: 98 W

Number of Output Voltages: 3

Voltage 1: 5 V

Current 1: 10 A

Voltage 2: 12 V

Current 2: 2 A

Voltage 3: 12 V

Rack Height: 3 U

Rack Width: 6 HP

## ADDITIONAL PRODUCT DETAILS

Pluggable 19" Power Supplies with H15 connector for fanless applications.

For Input voltage 100-360 VDC see AC/DC Switched mode power supply.

Please order front panel separately.

### **CERTIFICATIONS**





## North America

All locations +1.763.422.2661 Chat with us: schroff.nyent.com

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

nVent.com

#### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER