SIDE CUTTERS, TELEPHONE-AND COMBINATION-PLIERS

lap joint, bright polished, chrome plated, with dissipative black hand guard

cutting ca	pacity
------------	--------

				00	atting capacity		
No.	Length mm	Head width mm	Finish	Wire soft	mm medium	Ø hard	Weight g
Side cutt Swedish f							
3-133-13	145	19	special steel	4.0	2.5	1.3	165



snipe nose, long straight jaws, with wire cutter for hard wire

3-245-13 200 18 serrated jaws 195



with wire cutter, for hard wire

3-732-13 165 23 serrated jaws 185







NEW

ESD SPECIAL-PLIER

For gripping round screw heads. Optimal for opening defective screw connections.

No.	Length	Head width	Finish	Weight
	mm	mm		g

ESD special combination plier

3-734-13 120 12 ESD special combination plier, 120 mm, 90 polished, dissipative handles







NEW

WATER PUMP PLIER

with Push-Button

No.	Length	Finish	Weight
	mm		g

Water pump plier

3-573 180 Water pump pliers 180 mm, with push button,

extra slim head to access places difficult to reach, slip-resistant hand grips

180



3-573

