

Yealink DECT Handset

- New modern commercial design, more compact and easy to carry
- 2.4" 240 x 320 TFT color screen with intuitive user interface
- Up to 21 hours talk time (in ideal conditions)
- Up to 166 hours standby time (in ideal conditions)
- Quick charging: 10-min charge time for 2-hour talk time
- HD voice and noise cancellation
- Headset connection via Bluetooth or 3.5 mm jack
- Vibration alarm guarantee you not to miss any call even in noisy situations
- Sturdy and reliable belt clip to move freely
- Flexibly meet demands in either single-cell or multi-cell solutions



HD Audio



Noise Cancellation



3.5mm Headset Jack



Belt Clip



Quick Charge



Built-in Bluetooth 5.1



Vibration Alarm



OTA Upgrade

Yealink W78H is the high-end stylish modern wireless handset designed for business use with a new ID design, which has a 2.4" screen and is more sleek, convenient to carry, durable. W78H can provide you with a crystal-clear audio experience, never miss any important information.

With W78H, you can enjoy maximum freedom and flexibility. You can choose a Bluetooth headset or wired headset on your demand, thanks to the Bluetooth 5.1 and a 3.5mm headset jack. Thanks to the vibration alarm, you are guaranteed not to miss any call, even in noisy and stressful situations.

Combining the benefits of wireless communication with the rich business features of Voice-over-IP telephony empowers users with convenient wireless communication, excellent speech quality, and encrypted call information by the reliable DECT encryption technology. Its graphical color display will provide you with a comfortable and joyful user experience for the all-day work.

W78H is perfectly compatible with Yealink W70B. The W78P system can support 10 handsets, 10 SIP accounts, and 20 simultaneous calls (2 calls per handset).

Also, W78H will be perfectly compatible with the W80/W90 multi-cell system, allowing you seamless roaming and handover of the calls and providing you with more options for your office expansion.

DECT technology:

Yealink DECT technology is based on CAT-iq2.0, which focuses on high quality Audio VoIP (wideband), as well as low bit - rate data applications. But we are not compatible with any third-party DECT devices (base station, handset, etc.).

Display

- 1.8" 128x160 TFT color screen
- Intuitive user interface with icons and soft keys
- Caller ID with name and number
- Notification Light: voice mail, missed call
- Date & time (manual/auto synchronization)
- Screen saver
- Multilingual user interface
- Keypad backlight

Phone Features

- Up to 2 simultaneous calls per handset
- Handset select for receiving call
- Handset and Number select for making call
- Auto intercom, auto answer
- 3-way conference
- Call forward: Always/Busy/No Answer
- DND
- Call waiting, mute, hold
- Call transfer
- Swap between calls
- Redial
- Speed dial
- Voice mail
- Silence
- Dial plan: Replace Rule/Area Code/Block Out
- Keypad lock, emergency call
- 100 phone book memory (store in the base)
- Remote phonebook, LDAP, XML phonebook
- Phonebook search, block list
- Call history: All/Placed/Missed/Received (up to 100 entries)

- Direct IP call without SIP proxy
- Reset to factory, reboot
- Anonymous call, Anonymous call rejection
- OTA (Over-The-Air) upgrade

Voice Features

- Full-duplex speakerphone
- HD audio
- Hearing Aid Compatibility (HAC) compliant
- Frequency response—100 Hz–7 kHz
- FNR (Flexible Noise Reduction)/Noise Cancellation
- Receiver volume control: 5 steps
- Ringer volume control: 5 steps+off
- 9 ringer melodies
- Multiple advisory tones
- Acoustic warning for low battery status
- DTMF

Physical Features

- Handset Size: 151.0 mm x 49.5 mm x 21 mm
- Handset Weight: 98g
- Color: Space Gray
- Battery: 1010 mAh, Lithium-ion, 3.7 V, 3.73 WH
 - Up to 21 hours of talk time (in ideal conditions)
 - Up to 166 hours of standby time (in ideal conditions)
- Headset jack (3.5 mm)
- Charger: DC 5V/0.6A Output
- Power Adapter:
 - Input: 100-240 V ~ 50/60 Hz, 0.2 A
 - Output: 5 V, 0.6 A

- Backlit keypad with 25 keys:
 - Standard ITU telephone keypad, 12 keys, 4x3, with star and pound key
 - 5 navigation keys (left, right, up, down, OK)
 - 2 softkeys
 - 6 function keys (Speaker, message, Off-hook, Cancel, TRAN, Mute)
 - 6 shortcut keys
- Operating humidity: 10 ~ 95%
- Operating temperature: -10 ~ +50°C (+14~122°F)
- Storage temperature: -30 ~ 70°C (-22 ~ 158°F)

DECT

- Frequency bands:
 - 1880 – 1900 MHz (Europe), 1920 – 1930 MHz (US)
- DECT Range:
 - Up to 50 meters indoor (in ideal conditions)
 - Up to 300 meters outdoor (in ideal conditions)
- DECT Standards: CAT-iq2.0

Package Features

- Package contents:
 - W78H Handset
 - Charger Cradle
 - Rechargeable Battery
 - Belt Clip
 - Power Adapter
- Qty/CNT: 20 PCS
- Giftbox size: 181mm x 104mm x 90mm
- Carton meas: 473mm x 443mm x 198mm
- N.W: 6.884kg
- G.W: 7.696kg

Compliance

