

Quarter circle milling cutter HSSE Co 5

Concave

ORION[®]

Application:

Quarter circle milling cutter for machining complex forms, e.g. bore radii in materials up to 1000 N/mm².

Execution:

- Finishing teeth
- 5° cutting angle
- Up to 5 mm radius - backed off radially and axially
- From 5.5 mm radius - ground chamfers
- Up to 8 mm radius - combination shank in accordance with DIN 1835 B and D
- From 8.5 mm radius - straight shank in accordance with DIN 1835 B
- For mounting in self-clamping chucks, e. g. Clarkson, Bahnmüller



Art. no.	15461 035
Brand	ORION
Manufacturer Part Number	15461035
Surface	Uncoated
Type	N
Number of cutting edges	4 PCS
Tool holding device	HB combined shank
Radius	3.5 mm
Min. cutting edge diameter	6 mm
Max. cutting edge diameter	13 mm
Length	60 mm
Shank diameter	12 mm
fz steel 700	0.01 mm
Gross Weight	0.056 kg
Product Group	106

EAN

4039247097098