

## GWS 19-125 CI angle grinder

1900 W, 230 V, 50 Hz

**BOSCH**

### Delivery

Holding flange, protective cover, clamping nut, extra handle, two-hole spanner, in box



<b>Art. no.</b>	<b>70371 600</b>
<b>Brand</b>	BOSCH
<b>Manufacturer Part Number</b>	060179N002
<b>Model</b>	GWS 19-125 CI
<b>Manufacturer Article Number</b>	060179N002
<b>Battery included</b>	No
<b>Number of rechargeable batteries/batteries</b>	0
<b>Washer diameter</b>	125 mm
<b>Power input</b>	1900 W
<b>Power output</b>	1220 W
<b>Idle speed</b>	11500 rpm
<b>Thread dimension of spindle</b>	M14
<b>Weight</b>	3 kg
<b>With restart protection</b>	Yes
<b>With soft start</b>	Yes
<b>With overload protection</b>	Yes
<b>With electronic feedback</b>	Yes
<b>With reverse switch off</b>	No
<b>With disc brake</b>	No
<b>With dead man function</b>	No
<b>Gross Weight</b>	3.650 kg
<b>Product Group</b>	731

### EAN

3165140838375

