




DIN 6798 A

Standard withdrawn

350-425 HV



BN 781

Serrated lock washers

type A, external serrations

Spring steel 350-425 HV

zinc plated blue

- ~UNI 8842 A
- ~CSN 021745



ISO 4042

Fasteners hardness ≥ 320 HV with electroplated coatings:
Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the
introduction section.

Article#		d_1 min.	d_2 max.	s
1278002	M2	2,2	4,5	0,3
1437135	M2,3	2,5	5	0,4
1228919	M2,5	2,7	5,5	0,4
1278037	M3	3,2	6	0,4
1278045	M3,5	3,7	7	0,5
1278053	M4	4,3	8	0,5
1278061	M5a	5,1	9	0,5
1963597	M5	5,3	10	0,6
1278088	M6	6,4	11	0,7
1437143	M7	7,4	12,5	0,8
1278096	M8a	8,2	14	0,8
1963600	M8	8,4	15	0,8
1278118	M10	10,5	18	0,9
1278126	M12	13	20,5	1
1278134	M14	15	24	1
1278142	M16	17	26	1,2
1278150	M18	19	30	1,4
1278169	M20	21	33	1,4
1437178	M22	23	36	1,5
1278177	M24	25	38	1,5
1437186	M27	28	44	1,6
1437194	M30	31	48	1,6