

# CAB PCQ 403023 G



Sample image

**Order symbol :** CAB PCQ 403023 G

**Product nr :** 8113458

UL Code : 8143458

UL Name : UL CAB PCQ 403023 G

**Description :** Cabinet, PC


**Remarks :** Grey cover

**EAN :** 6418074011176

**El. number :**

- Finland : 3421978
- Denmark :
- Sweden : 2539130

**Including :** Base with screws for mounting plate/DIN-rail. internal corner plugs. cover with PUR gasket and CS 12137 cover screws.



**Dimensions :**                      **Height**                      **Width**                      **Depth**

mm :                                      400                                      300                                      230

inch :

**Accessories :**

DRF 43/44    DIN rail frame set, for enclosures:

PAT 12040    Hinge set

MB 12225    Swing door set  
AL

EKIV 37        DIN-35 Mounting rail, for enclosures:  
(366 x 35 x 1)

**Materials :**

Material :	Polycarbonate
Base colour :	RAL 7035 -light grey
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

EKIV 27	DIN-35 Mounting rail, for enclosures: (266 x 35 x 1)
EKIV 43	Mounting plate, for enclosures: (370 x 270 x 1)
FP A 43	Swing-out door/Front plate (aluminium), for enclosures: (268 x 368 x 1)

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

**Rating :**

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
Electrical insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance :	UL 508
Flammability Rating :	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C :	960 °C
NEMA Class	

**Certificates :**

Certificate FI 40848