


Fork cable lug

Heat-shrinkable Fork Cable Lugs, Insulated



SPECIFICATION:

Insulation material	Polyethylene
Surface material	Tin-plated
Voltage	600 V
Material	Copper
Shrinkage temperature range	+150 °C
Shrinkage temperature max.	+150 °C
Shrinkage temperature min.	+150 °C

PRODUCT RANGE:

Art. Nr.	Cross-section	Diameter	Colour	Temperature range	Thickness
RND 465-00179	0.5...1.5 mm ²	3.7 mm	red	max. +105 °C	0.75 mm
RND 465-00180	0.5...1.5 mm ²	4.3 mm	red	max. +105 °C	0.75 mm
RND 465-00181	0.5...1.5 mm ²	5.3 mm	red	max. +105 °C	0.75 mm
RND 465-00182	1.5...2.5 mm ²	3.7 mm	blue	max. +105 °C	0.8 mm
RND 465-00183	1.5...2.5 mm ²	4.3 mm	blue	max. +105 °C	0.8 mm
RND 465-00184	4...6 mm ²	4.3 mm	yellow	max. +105 °C	1.0 mm