




Technical Data Sheet

Description

Description	92 ABEK/St					
Part Number	10097995					
Marking according to EN	A2, B2, E2, K1 - P2					
Conditions of use	<ul style="list-style-type: none"> organic gases and vapors with a boiling point > 65° C inorganic gases and vapors, e.g. chlorine, hydrogen sulfide, hydrogen cyanide sulfur dioxide, hydrogen chloride and other acid gases ammonia and organic ammonia derivatives particles 					
Colour code	<table border="1"> <tr><td>brown</td></tr> <tr><td>grey</td></tr> <tr><td>yellow</td></tr> <tr><td>green</td></tr> </table>	brown	grey	yellow	green	
brown						
grey						
yellow						
green						
labels						

Characteristics

Weight [g]	295
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148 - 1

Breathing Resistance

	at	EN 14387 requirements	Typical values
	30 l / min	2,1 mbar	1,50 mbar
	95 l / min	8,0 mbar	5,25 mbar

Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]

Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C ₆ H ₁₂]	35 min	45 min
B2	chlorine [Cl ₂]	20 min	40 min
	hydrogen sulfide [H ₂ S]	40 min	55 min
	hydrocyanic acid [HCN]	25 min	45 min
E2	sulfur dioxide [SO ₂]	20 min	22 min
K1	ammonia [NH ₃]	50 min	60 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P2	sodium chloride [NaCl]	6.00%	< 0,50 %
	paraffin oil	6.00%	< 0,50%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / impregnated activated carbon

Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6 years
---------------------------	--