

## MOSA M12 male 0° X coded (IDC)

Gbit Ethernet

M12

Male straight


8-pole, shielded

Clamping range cable entry: 5.5...9 mm



X-coded, 8-pole

### [Link to Product](#)

#### Illustration



## Male



Product may differ from Image

**Form**

21101

**Technical Data**

Operating voltage	50 V AC/60 V DC
Operating current per contact	max. 0.5 A
Connection cross section	0.14...0.34 mm <sup>2</sup>
Sealing range (cable diameter)	5.5...9.0 mm
Protection	IP67 inserted and tightened (EN 60529)
Housing	CuZn, nickel plated

**General data**

Temperature range	-40...+85 °C
-------------------	--------------

**Commercial data**

country of origin	DE
customs tariff number	85369010
minimum order quantity	1