



WALL BRACKET TYPE 10 FOR MOBILE PANEL 170, MOBILE PANEL 177, MOBILE PANEL 277, MOBILE PANEL 277 IWLAN, MOBILE PANEL 277F IWLAN, MOBILE CLIENT900, WITHOUT MOUNTING PARTS AMOUNT: SEE TECHNICAL DATA

Product type designation	
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	No
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	
Type of housing (front)	
• Sheet metal	Yes; Powder-coated
Dimensions	
Width	200 mm
Height	230 mm
Depth	25 mm; Constructive

Weights

Without packaging 550 g; Without cable holder

Scope of supply

Delivery unit in items 1; Color: Black

other

Note: Mobile Panel 170, Mobile Panel 177, Mobile Panel 277 IWLAN, Mobile Panel 277F IWLAN, without mounting parts

Usable in the following products

- Product 1 [6AV6545-4BA16-0CX0](#)
- Product 2 [6AV6545-4BB16-0CX0](#)
- Product 3 [6AV6545-4BC16-0CX0](#)
- Product 4 [6AV6645-0AA01-0AX0](#)
- Product 5 [6AV6645-0AB01-0AX0](#)
- Product 6 [6AV6645-0AC01-0AX0](#)
- Product 7 [6AV6645-0BA01-0AX0](#)
- Product 8 [6AV6645-0BB01-0AX0](#)
- Product 9 [6AV6645-0BC01-0AX0](#)
- Product 10 [6AV6645-0DD01-0AX0](#)
- Product 11 [6AV6645-0CB01-0AX0](#)
- Product 12 [6AV6645-0DB01-0AX0](#)
- Product 13 [6AV6645-0DC01-0AX0](#)

last modified:

12.03.2015