

Product information

70 05 140

Diagonal Cutter

DIN ISO 5749



- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened





General	
Article No.	70 05 140
EAN	4003773039488
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	154 g
Dimensions	140 x 55 x 19 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 2.5 mm
Cutting capacities hard wire (diameter)	Ø 1.8 mm

technical change and errors excepted

KNIPEX Quality – Made in Germany











