



Wiha SoftFinish® Handle - Standard Series



302 Slotted Screwdriver, With Wiha-SoftFinish® Handle Round blade, high alloy CVM, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	↓	↓	←	←	⊖	⊖	←	←	⊕	⊕	↶	↷
	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
30202*	2.0	.079	65	2.6	0.4	.016	169	6.7	23	.91	.05	10
30203*	2.5	.098	75	3.0	0.4	.016	179	7.0	23	.91	.05	10
30204*	3.0	.118	80	3.1	0.5	.020	184	7.2	23	.91	.06	10
30205*	3.0	.118	100	3.9	0.5	.020	204	8.0	23	.91	.06	10
30206*	3.0	.118	150	5.9	0.5	.020	254	10.0	23	.91	.07	10
30208*	3.0	.118	200	8.0	0.5	.020	304	12.0	23	.91	.07	10
30210*	3.5	.139	100	3.9	0.6	.024	204	8.0	23	.91	.07	10
30212*	3.5	.139	200	8.0	0.6	.024	304	12.0	23	.91	.09	10
30215*	4.0	.157	100	3.9	0.8	.031	211	8.3	30	1.18	.11	10
30217*	4.0	.157	150	5.9	0.8	.031	261	10.3	30	1.18	.12	10
30216*	4.0	.157	200	8.0	0.8	.031	311	12.2	30	1.18	.14	10
30218*	4.5	.187	80	3.1	0.8	.031	191	7.5	30	1.18	.11	10
30211*	4.5	.187	125	5.0	0.8	.031	236	9.3	30	1.18	.12	10
30219*	4.5	.187	150	5.9	0.8	.031	261	10.2	30	1.18	.12	10
30220*	5.5	.216	125	5.0	1.0	.039	236	9.3	30	1.18	.15	10
30238*	5.5	.216	300	11.8	1.0	.039	411	16.1	30	1.18	.24	10
30221*	5.5	.216	200	8.0	1.0	.039	311	12.2	30	1.18	.20	10
30222	6.0	.250	100	3.9	1.2	.047	218	8.6	36	1.42	.17	10
30223	6.5	.255	100	3.9	1.0	.039	218	8.6	36	1.42	.20	10
30225	6.5	.255	150	5.9	1.2	.047	268	10.6	36	1.42	.22	10
30226	6.5	.255	200	8.0	1.2	.047	318	12.5	36	1.42	.22	10
30227	8.0	.315	150	5.9	1.2	.047	274	10.8	41	1.61	.29	10
30230	8.0	.315	175	7.0	1.2	.047	299	11.8	41	1.61	.30	10
30232	8.0	.315	300	11.8	1.2	.047	424	16.7	41	1.61	.36	10
30235	10.0	.393	200	8.0	1.6	.063	324	12.8	41	1.61	.36	10
30236	12.0	.472	250	9.8	2.0	.078	374	14.7	41	1.61	.52	10

*Cabinet Tips



311 Phillips Screwdriver, With Wiha-SoftFinish® Handle Round blade, high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	⊕	←	←	↓	↓	←	←	⊕	⊕	↶	↷
	Size	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
31105	0	60	2.4	3.0	.118	164	6.5	23	.91	.06	10
31110	1	80	3.1	4.5	.177	191	7.5	30	1.18	.11	10
31112	1	200	8.0	4.5	.177	311	12.3	30	1.18	.15	10
31114	1	300	12.0	4.5	.177	411	16.2	30	1.18	.18	10
31115	2	100	3.9	6.0	.236	218	8.6	36	1.42	.20	10
31117	2	200	8.0	6.0	.236	318	12.5	36	1.42	.25	10
31118	2	300	12.0	6.0	.236	418	16.5	36	1.42	.30	10
31120	3	150	5.9	8.0	.315	274	10.8	41	1.61	.33	10
31125	4	200	8.0	10.0	.393	323	12.7	41	1.61	.51	10



30294 6 Pc. Slotted/Phillips Screwdriver Set

Item No.	↓	←	⊕	←	↶	↷
	mm	mm	Size	mm	lbs.	
30294	4.0	100	1	80	1.29	
	6.5	150	2	100		
	8.0	150				
	4.0*	25				

*Stubby screwdriver with Wiha SoftFinish® handle



30298 8 Pc. Slotted/Phillips Screwdriver Set

Item No.	↓	←	⊕	←	↶	↷
	mm	mm	Size	mm	lbs.	
30298	3.0	100	1	80	1.87	
	4.0	100	2	100		
	5.5	125	3	150		
	6.5	150				
	8.0	175				



30297 12 Piece Slotted & Phillips Screwdriver Set

Item No.	↓	←	⊕	←	↶	↷
	mm	mm	Size	mm	lbs.	
30297	3.0	100	0	60	2.48	
	4.0	100	1	80		
	5.5	125	2*	25		
	6.5	150	2	100		
	6.5*	25	3	150		
	8.0	175				
	10	200				

*Stubby screwdriver with Wiha SoftFinish® handle