

XAWF178EX

control station - XAW-F - metal - 1 NC + 1 NC - red -
Emergency Stop



Main

Range of product	Harmony XAW
Product or component type	Complete control station
Device short name	XAWF
Control station application	Emergency stop function
Material	Metal
Reset	Turn to release
Control station composition	1 mushroom head Ø 40 mm push-button, red trigger action 1 NC + 1 NC

Complementary

Colour of base of enclosure	Black
Colour of cover	Black
Cable entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	77 mm
Height	80 mm
Marking	Ex tb IIIC T85°C Db IP65
Mechanical durability	300000 cycles
Short-circuit protection	10 A cartridge fuse type gG
[Ie] rated operational current	3 A at 240 V AC-15, A600 0.1 A at 600 V DC-13, Q600 0.55 A at 125 V DC-13, Q600 1.2 A at 600 V AC-15, A600 0.27 A at 250 V DC-13, Q600 6 A at 120 V AC-15, A600

Environment

ambient air temperature for operation	-20...60 °C
overvoltage category	I conforming to IEC 60536
IP degree of protection	IP65 IEC 60529
standards	EN/IEC 60947-5-1 EN/IEC 60947-1 EN 61000-6-2 EN 60079-0 : 2009 EN 60079-31 : 2009 IEC 60079-0 : 2007 IEC 60079-31 : 2008 EN/ISO 13850 EN 60947-5-4 EN 60947-5-5
directives	94/9/EC - ATEX directive
dust zone	Zone 21 - 22
product certifications	INERIS 04ATEX0023X

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------