Searchable Features:	
Brand:	AMP
Header Type:	Breakaway
No. of Rows:	Single
No. of Positions:	50
Profile:	Standard
Centerline, Matrix (mm [in]):	2.54 [.100]
Mount Angle:	Vertical
Selectively Loaded:	No
PCB Retention Feature:	Without
Surface Mount Compatible:	No
Contact Mating Area Plating:	Gold (30)
Board Standoff:	Without
Mounting Ears:	Without
Panel Attachment:	No
Mating Connector Lock:	Without
High Temperature Housing:	No
High Speed Serial Data Connector:	No
Termination Post Length (mm [in]):	3.20 [0.126]

Other Properties:	
Contact Material:	Brass
Housing Material:	Thermoplastic Polyester
Contact Termination Area Plating:	Tin
Housing Flammability Rating:	UL 94V-0
Packaging Method:	Box
Packaging Quantity:	500