


CONSTRUCTION:



PINT:

DESCRIPTION:

- CONDUCTOR: 7/0.12mm, 28AWG;
- INSULATOR: PVC, OD=0.85mm.

Electrical properties:

- Current rating: 1Amp
- AC withstand voltage: 500V / 1 minute
- The insulation resistance: 1000MΩ Min at DC 500V
- Contact resistance: 30 mΩ Max at DC 100mA
- Working temperature: - 55° C to 105° C

P/N	Description
CB23221	8 WAY 30.5M
CB14768	9 WAY 30.5M
CB23222	10 WAY 30.5M
CB14769	14 WAY 30.5M
CB23223	15 WAY 30.5M
CB14770	16 WAY 30.5M
CB14771	20 WAY 30.5M
CB23224	24 WAY 30.5M
CB14772	26 WAY 30.5M
CB23225	34 WAY 30.5M
CB23226	40 WAY 30.5M
CB23227	50 WAY 30.5M

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance			
Flat Ribbon Cable-D series				x.	± 0.2	x."	± 2"
				x	± 0.1	.x"	± 1"
				.xx	± 0.05	.xx"	± 0.5"
				.xxx	± 0.01		
图名 /File name		文件编号 /File No.		单位 /Units: mm			
备注 /Remark		页序 /Sheet					