

Fluorescent T8 (Bakery)

F30W T8 FoodStar Bread
0001862

Product features



PRODUCT OVERVIEW

Product name	F30W T8 FoodStar Bread
Technology	Fluorescent
Watt (Rated) (W)	30.00
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940492
E-number Norway	3815478
Colour temperature (K)	2300
Light colour	Foodstar Bread
CRI (Ra)	83
Colour Variation Initial (SDCM)	SDCM5
Wattage (W)	30.00
Product Voltage (V)	96
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	24000
Product EAN number	5410288018621

DATA TABLE

General data

Product name	F30W T8 FoodStar Bread
Technology	Fluorescent
Watt (Rated) (W)	30.00
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13

Fluorescent T8 (Bakery)

F30W T8 FoodStar Bread
0001862

Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940492
E-number Norway	3815478

Optical data

Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	2300
Correlated colour temperature range (K)	2100 - 2500
Light colour	Foodstar Bread
CRI (Ra)	83
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N

Electrical data

Wattage (W)	30.00
Equivalent watt (W)	30
Watt (Rated) - High frequency (W)	24.00
Current (A)	0.365
Product Voltage (V)	96
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	365
Lamp Energy Label (class)	G

Lifetime data

Average life (Nominal) (h)	24000
----------------------------	-------

Physical data

Nominal Product Length (mm)	900.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	894.4
Length base to pin Min-Max (mm) - B	899.3-901.7
Max. Lamp Length (mm) - C/L	908.8
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.122

Packaging

Single packaging type	Carton
Product EAN number	5410288018621
Packaging single length / height (cm)	90.9
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288018628

Fluorescent T8 (Bakery)

F30W T8 FoodStar Bread

0001862

Units per outer package	25
Packaging outer length / height (cm)	93.5
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data

Lamp mercury content (mg)	4.50
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Suitable for household illumination	No

TECHNICAL DRAWINGS

