

Coloured T8 F58W/BLUE 0002571



Product features

- Coloured T8



PRODUCT OVERVIEW

Product name	F58W/BLUE
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
ETIM Class	EC000108
Luminous flux (lm)	1000
Light colour	Blue
Wattage (W)	58.00
Product Voltage (V)	110
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	8000
Product EAN number	5410288025711

DATA TABLE

General data

Product name	F58W/BLUE
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open

Coloured T8 F58W/BLUE 0002571

General application	SPG
ETIM Class	EC000108

Optical data

Luminous flux (lm)	1000
Ambient temperature for maximum luminous flux (°C)	25
Light colour	Blue
Adjustable chromaticity	N

Electrical data

Wattage (W)	58.00
Watt (Rated) - High frequency (W)	50.00
Current (A)	0.670
Product Voltage (V)	110
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	670

Lifetime data

Average life (Nominal) (h)	8000
Average life (Rated) (h)	8000

Physical data

Nominal Product Length (mm)	1500.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	1500.0
Length base to pin Min-Max (mm) - B	1504.7-1507.1
Max. Lamp Length (mm) - C/L	1514.2
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.2

Packaging

Single packaging type	Carton
Product EAN number	5410288025711
Packaging single length / height (cm)	151.1
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288025718
Units per outer package	25
Packaging outer length / height (cm)	154.5
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data

Lamp mercury content (mg)	2.80
Breakage cleaning instructions	Applicable

Coloured T8 F58W/BLUE 0002571

Special purpose lamp	Yes
Suitable for household illumination	Yes

TECHNICAL DRAWINGS

