

Solder Terminal 0.7x11.2mm 90° Brass,tinned 0.6mm/hole 0.8mm
13.19.125

Product No. 13.19.125

Type	Stamped Terminals
Model	PC-Terminal Horizontal
Design	90°Solder Pin
Mounting Hole Dia.	0.80 mm
Broad or Diameter	0.00 mm
Material	Brass CuZn37
Plating	Tin-Plated
Shaft Length T/L1	3.00 mm
Special	Surface silver = 13.19.129
Length	11.20 mm
Pieces per Reel	0.00 pcs
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products Solder Terminal 0.7x11.2mm 90°
Brass,silver-pl./0.6mm/hole 0.8mm
13.19.129

