

Instruction Leaflet

GB

Thank you for purchasing this quality LED lamp.
Please read these instructions carefully before using your lamp.



DESCRIPTION	LED Task Lamp
MANUFACTURER REF.s	LC8025LED
VOLTAGES AVAILABLE	220v - 240v, 50Hz
LIGHT TYPE	SMD LED 84pc, 90 CRI
DIMMER	Built-in dimmer
CABLE LENGTH	1.5m
TABLE CLAMP/BASE	Table Clamp

HOW TO USE

1. Securely fasten the table clamp included to a solid horizontal surface with thicknesses between 12.5 - 62.5mm (0.5 - 2.5"). Ideal for household tables, study desks and work benches
2. Insert the stem of the lamp into the clamp hole
3. Insert the 220v - 240v plug into a conveniently located electrical socket
4. Switch the lamp on by using the on/off switch located on top of the head. The lamp is now ready to use.
5. Adjust your lamp head position to suit your need and tighten the locking nuts as required

IMPORTANT! - SAFETY INSTRUCTIONS

WARNING: When using electrical products, important safety precautions must be adhered to in order to reduce the risk of fire, electric shock and personal injury.

PLEASE READ THE FOLLOWING CAREFULLY:

1. Indoor use only:
 - a. Room temperature from -5 to +40 degrees centigrade
 - b. Humidity: Less than or equal to 95%
2. Do not expose the lamp to:
 - a. High temperatures
 - b. Water, steam or damp conditions
 - c. Corrosive, flammable liquids, or gaseous / explosive atmospheres
 - d. Direct sunlight
3. Do not abuse the cord. Never carry the lamp by the cord or pull the cord to disconnect the lamp. Keep the cord away from heat, oil or sharp objects
4. Disconnect your lamp when not in use and when changing the lens
5. Never attempt to disassemble or repair the lamp, unless you are a qualified electrician

CE Declaration of Conformity

We declare that this product complies with the Electromagnetic Compatibility Directive, the Low Voltage Directive & RoHS



RoHS Compliant

LightCraft

Shesto, Sunley House, Olds Approach, Watford WD18 9TB
+44 (0) 20 8451 6188 sales@shesto.co.uk
www.shesto.com