


## Lumina

Lumina Wave LED 2700K

3039987



### Product features

- Ambient decorative Wave LED rectangular vertical wall light with direct / indirect lighting to provide a soft lighting effect, 2700K amber white colour temperature, white aluminium body and integrated LED (non-dimmable) driver, 211 lumens, 6W, 35lm/W, 2700K, IP20, RAL 9003



## PRODUCT OVERVIEW

Product name	Lumina Wave LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted
Environment	Internal
General application	Hospitality, Residential & Consumer
ETIM Class	EC002892
E-number FI	4271126
E-number SE	7502642
Warranty	3 years
Fixture luminous flux (lm)	211
Luminaire efficacy (lm/W)	35
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Total power consumption (W)	6
Electrical protection	Class II
Control gear type	LED driver constant current
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	8711971399872

## DATA TABLE

### General data

Product name	Lumina Wave LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted

## Lumina

*Lumina Wave LED 2700K*

3039987

Environment	Internal
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4271126
E-number SE	7502642
Warranty	3 years

### Optical data

Fixture luminous flux (lm)	211
Luminaire efficacy (lm/W)	35
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Adjustable chromaticity	N

### Electrical data

Total power consumption (W)	6
Mains voltage (V)	100-240V
Electrical protection	Class II
Control gear type	LED driver constant current
Transformer required	No
Dimming method	N/A
Drive current (mA)	500
Energy Efficiency Class (A->G) of contained light source	F

### Lifetime data

Lifespan L70 B50	50000
Lifespan L80 B20	35000
Lifespan L90 B10	25000

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	78
Nominal Product Width (mm)	254
Nominal Product Height (mm)	64
Weight (kg)	0.49

### Packaging

Single packaging type	Carton
Product EAN number	8711971399872
Packaging single length / height (cm)	26.0
Packaging single width (cm)	10.0
Packaging single depth (cm)	7.5

## Lumina Lumina Wave LED 2700K 3039987


DUN14 (outer)	18711971399879
Units per outer package	20
Packaging outer length / height (cm)	41.5
Packaging outer width (cm)	39.0
Packaging outer depth (cm)	27.5

### PHOTOMETRY

0.5	1.51	E(0°) E(C0)	56.5°	275 23
1.0	3.02	E(0°) E(C0)	56.5°	69 6
1.5	4.53	E(0°) E(C0)	56.5°	31 3
2.0	6.04	E(0°) E(C0)	56.5°	17 1
2.5	7.55	E(0°) E(C0)	56.5°	11 1
3.0	9.07	E(0°) E(C0)	56.5°	8 1

Distance [m]      Cone diameter [m]      Illuminance [lx]

— C0 - C180 (Half beam angle: 113.0°)



### TECHNICAL DRAWINGS

