

Die, HSS PG right, pre-slotted and 1.75 thread chamfer

For universal use up to 700 N/mm²

ORION[®]

Application:

For tapping male armoured pipe threads in the steel, stainless steel, NF metals and special alloy material groups up to a strength of 700 N/mm².

Execution:

- Right-handed die with spiral point, pre-slotted, 1.75-threaded chamfer

Advantage:

- Innovative cutting geometry for high process reliability



Art. no.	13491 110
Brand	ORION
Manufacturer Part Number	13491110
Thread type	PG
Cutting material	HSS
Thread type x nominal diameter in inches	PG 11 in
Number of thread starts per inch	18
Outer diameter	45 mm
Height	14 mm
Cutting direction	Right-hand cutting
DIN	40434
Gross Weight	0.113 kg
Product Group	1DC

EAN

4039247074907