

Grooving lathe chisel, HSSE, square

for internal grooving, for universal use up to 1300 N/mm²

ORION[®]

Application:


For internal grooving in steel, (stainless steel), cast iron, non-ferrous metals and (special alloys) material groups up to a strength of 1300 N/mm².

Execution:

- butt-welded design with varnished and square shank

Advantage:

- wear-resistant cutting material and high-quality grinding ensure a long service life



Art. no.	17091 320
Brand	ORION
Manufacturer Part Number	17091320
Shank width	20 mm
Shaft height	20 mm
Length	220 mm
Recessing width	4 mm
Max. turning depth	8 mm
DIN	Similar to 4963
Gross Weight	0.700 kg
Product Group	159

EAN

4039247943678