

## sheet metal nibbler BLK 1.6 E

350 watts



### Application:

ideal for flexible and universal application for plate thicknesses of up to 1.6 mm

### Version:

- tool-free, rotatable die carrier allows cutting direction to be set through 360° in 45° steps.
- QuickIN quick-change system



<b>Art. no.</b>	<b>70375 500</b>
<b>Model</b>	BLK 1.6 E
<b>Manufacturer Article Number</b>	72323860000
<b>Max. cutting capacity in sheet metal (400 N/mm<sup>2</sup>)</b>	1.6 mm
<b>Max. cutting capacity in sheet metal (600N/mm<sup>2</sup>)</b>	1 mm
<b>Max. cutting capacity in sheet metal (800N/mm<sup>2</sup>)</b>	0.7 mm
<b>Max. cutting capacity in aluminium sheet (250 N/mm<sup>2</sup>)</b>	1.6 mm
<b>Cutting speed</b>	1.9 m/min
<b>Cutting lane width</b>	5 mm
<b>Immersion diameter</b>	22 mm
<b>Min. radius</b>	35 mm
<b>Power input</b>	350 W
<b>Power output</b>	210 W
<b>Stroke rate</b>	1500 rpm
<b>Weight</b>	1.8 kg
<b>Cable length</b>	5 m

### EAN-Code

4014586869858