

[Products](#) [Multimeter](#) [Digital handheld multimeter](#) [PeakTech® 3335](#)

PeakTech® 3335 PROD-ID: P 3335

[BACK](#)

Digital Multimeter ~ 2.000 Counts ~ 600V AC/DC ~ 10A AC/DC - Manu.-Range

3 ½ digits Digital Multimeter with a special design with a 38 mm Jumbo-display for easy reading, even the worst or darkest conditions thanks to its obviously screen size and its LCD backlight. Manual range, auto power off and data hold functions along with all the measuring values like capacitance, temperature, voltage, current, resistance and frequency made this multimeter suitable for educations sector and service.

- 38 mm LCD display, max. 2000
- Auto power off; manual ranging; Data hold function
- Continuity- and diode test
- Temperature-, Frequency- and Capacitance Test
- Safety: EN 61010-1; CAT III 600 V
- Accessories: Test leads, Type-K-Thermocouple probe, battery and operation manual



MANUAL

[PeakTech_3335_5s_12-2018E.pdf \(989.1 kB\)](#)

PICTURES

[3335_Front.jpg \(314.3 kB\)](#)

[3335_L.jpg \(292.9 kB\)](#)

[3335_R.jpg \(293.4 kB\)](#)

[3335_Rear.jpg \(244.9 kB\)](#)

DCV	200 mV/2/20/200/600 V - 100 μ V; \pm 0,5% + 2 dgt.
ACV	2/20/200/600 V - 1 m V; \pm 1% + 3 dgt. Frequency range: 40 .. 100 Hz
DCA	2/20/200 mA/10 A - 1 μ A; \pm 1% + 3 dgt.
ACA	2/200 mA/10 A - 1 μ A; \pm 1,2 % + 3 dgt. Frequency range: 40 .. 100 Hz
Ohm	200 Ω /2/20/200 k Ω /2/20 M Ω - 0,1 Ω ; \pm 1% + 2 dgt.
Capacitance	2/20/200 nF/2/200 μ F - 1 pF; \pm 4 % + 3 dgt.
Frequency	20 kHz - 0,01 Hz; \pm 1,5 % + 5 dgt.
Temperature	-20° C ... + 760° C -1° C; \pm 3 % + 3 dgt.
Operation voltage	9 V Battery
Dimensions (W x H x D)	92 x 195 x 38 mm
Weight	380 g
EAN-13	4250569400834

