

Industrial Style Thermocouple with Terminal Head



- Type K: Stainless steel 310 Sheath
- Type J: Stainless steel 321 Sheath
- Calibration type K or J
- Weatherproof aluminium IP67 terminal head with screw fit lid
- 6mm Diameter
- 100, 150, 200, 300, 400, 500 & 600 mm lengths available
- M20x1.5mm cable entry
- Type K Sensor range -100 to 1100deg C
- Type J Sensor range -100 to 760deg C

T/C Type	Probe Size	Manufacturer's Part Number	Rapid Part Number
K	6.0 x 100 mm	XE-3249-001	61-3171
K	6.0 x 150 mm	XE-3250-001	61-3172
K	6.0 x 200 mm	XE-3252-001	61-3173
K	6.0 x 300 mm	XE-3251-001	61-3174
K	6.0 x 400 mm	XE-3254-001	61-3175
K	6.0 x 500 mm	XE-3253-001	61-3176
K	6.0 x 600 mm	XE-3255-001	61-3177
J	6.0 x 100 mm	XE-3256-001	61-3178
J	6.0 x 150 mm	XE-3257-001	61-3179
J	6.0 x 200 mm	XE-3258-001	61-3180
J	6.0 x 300 mm	XE-3259-001	61-3181
J	6.0 x 400 mm	XE-3260-001	61-3182
J	6.0 x 500 mm	XE-3261-001	61-3183
J	6.0 x 600 mm	XE-3262-001	61-3184