


# E11190



## Adapter plug

ESTGF040MSS00,5E04 (M8)



1 O-ring

### Electrical data

Operating voltage [V]	< 45 AC / < 70 DC
Protection class	III

### Operating conditions

Ambient temperature [°C]	-25...85
Protection	IP 67

### Mechanical data

Weight [g]	12
Materials	brass nickel-plated

### Remarks


Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Cable: 0.5 m, PVC; 4 x 0.25 mm<sup>2</sup>

### Electrical connection - plug

Connector: 1 x M8, straight; Moulded body: brass, nickel-plated




# E11190



## Adapter plug

ESTGF040MSS00,5E04 (M8)

### Connection



Core colours :

BK = black  
BN = brown  
BU = blue  
WH = white