




ADOGH080MSS00.3K05STGK120MSS

Connection technology



**Product characteristics**

Jumper

M23 plug / M12 socket

Gold-plated contacts

Electrical data

Electrical design

AC/DC

Operating voltage [V]

30 AC / 36 DC

Environment

Ambient temperature [°C]

-20...90

Protection

IP 67

Mechanical data

Design

straight / straight

Material body

plug: Brass; Socket: TPU

Material nut

Brass; nickel-plated

Weight [kg]

0.111

Electrical connection




Connection

PUR cable / 0.3 m; 5 x 0.25 mm<sup>2</sup>; Ø 6 mm; screened, screen connected to the nut

Sheath colour

black

**Wiring**



Remarks

Pack quantity

[piece]

1