

Product information

X-treme Plus range – A3389DPL

d1 mm m7	Ø inches/ no.	d2 mm h6	l1 mm	l2 mm max.	l4 mm	Order code A3389DPL...
7.400		8	91	53	36	-7.4
7.500		8	91	53	36	-7.5
7.541	19/64 IN	8	91	53	36	-19/64IN
7.800		8	91	53	36	-7.8
7.900		8	91	53	36	-7.9
7.938	5/16 IN	8	91	53	36	-5/16IN
8.000		8	91	53	36	-8
8.100		10	103	61	40	-8.1
8.200		10	103	61	40	-8.2
8.300		10	103	61	40	-8.3
8.334	21/64 IN	10	103	61	40	-21/64IN
8.400		10	103	61	40	-8.4
8.500		10	103	61	40	-8.5
8.600		10	103	61	40	-8.6
8.700		10	103	61	40	-8.7
8.731	11/32 IN	10	103	61	40	-11/32IN
8.800		10	103	61	40	-8.8
9.000		10	103	61	40	-9
9.128	23/64 IN	10	103	61	40	-23/64IN
9.200		10	103	61	40	-9.2
9.300		10	103	61	40	-9.3
9.500		10	103	61	40	-9.5
9.525	3/8 IN	10	103	61	40	-3/8IN
9.600		10	103	61	40	-9.6
9.700		10	103	61	40	-9.7
9.800		10	103	61	40	-9.8
9.922	25/64 IN	10	103	61	40	-25/64IN
10.000		10	103	61	40	-10
10.100		12	118	71	45	-10.1
10.200		12	118	71	45	-10.2
10.300		12	118	71	45	-10.3
10.319	13/32 IN	12	118	71	45	-13/32IN
10.400		12	118	71	45	-10.4
10.500		12	118	71	45	-10.5
10.716	27/64 IN	12	118	71	45	-27/64IN
10.800		12	118	71	45	-10.8

d1 mm m7	Ø inches/ no.	d2 mm h6	l1 mm	l2 mm max.	l4 mm	Order code A3389DPL...
11.000		12	118	71	45	-11
11.100		12	118	71	45	-11.1
11.113	7/16 IN	12	118	71	45	-7/16IN
11.200		12	118	71	45	-11.2
11.500		12	118	71	45	-11.5
11.509	29/64 IN	12	118	71	45	-29/64IN
11.700		12	118	71	45	-11.7
11.800		12	118	71	45	-11.8
11.906	15/32 IN	12	118	71	45	-15/32IN
12.000		12	118	71	45	-12
12.100		14	124	77	45	-12.1
12.200		14	124	77	45	-12.2
12.300		14	124	77	45	-12.3
12.303	31/64 IN	14	124	77	45	-31/64IN
12.500		14	124	77	45	-12.5
12.600		14	124	77	45	-12.6
12.700	1/2 IN	14	124	77	45	-1/2IN
13.000		14	124	77	45	-13
13.300		14	124	77	45	-13.3
13.494	17/32 IN	14	124	77	45	-17/32IN
13.500		14	124	77	45	-13.5
14.000		14	124	77	45	-14
14.288	9/16 IN	16	133	83	48	-9/16IN
14.500		16	133	83	48	-14.5
15.000		16	133	83	48	-15
15.500		16	133	83	48	-15.5
15.875	5/8 IN	16	133	83	48	-5/8IN
16.000		16	133	83	48	-16
16.500		18	143	93	48	-16.5
17.000		18	143	93	48	-17
17.500		18	143	93	48	-17.5
18.000		18	143	93	48	-18
19.050	3/4 IN	20	153	101	50	-3/4IN
20.000		20	153	101	50	-20