

Push Rivet

72.13.341

Product No. 72.13.341

Model	Push Rivets
Design	Head Style No. 1+2
Mounting Hole Dia.	3.2-3.7 mm
Panel Thickness	0.8-3.6 mm
Length	5.00 mm
Material	Nylon-6 UL94 V-2 / E41871
Color	Natural
Head Diameter	4.80 mm
Head Height	1.3mm
Prong Diameter	2.00 mm
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products

- Push Rivet
72.13.340
- Drive Rivet ø3.0mm/1.0-4.0mm panel
Polyamid 6.6,black
72.14.340
- Drive Rivet ø3.0mm/1.0-4.0mm panel
Polyamid 6.6,natural
72.14.341

