

Click Flat Diffusers

Cover C9 click 2m opal
0022620



Product features

- A click diffuser made of acrylic thermoplastic (PMMA). Operating temperature: -20 - 70 [°C]. IK rating: 08. UV resistant. Fire hazard certificate according to IEC 60695-2-11. Compatible with the following profiles: Profile deep wide surface 30 CDE-9/T (0022599), Profile shallow wide surface 30 CDE-9/T (0022600). Transparency level 75%.



PRODUCT OVERVIEW

| | |
|---------------------|------------------------|
| Product name | Cover C9 click 2m opal |
| Technology | Accessory |
| Housing | Aluminium |
| General application | Retail |
| ETIM Class | EC002557 |
| E-number FI | 4278037 |
| Warranty | 3 years |
| Housing colour | Silver |
| Product EAN number | 5410288226200 |

DATA TABLE

General data

| | |
|---------------------|------------------------|
| Product name | Cover C9 click 2m opal |
| Technology | Accessory |
| Housing | Aluminium |
| General application | Retail |
| ETIM Class | EC002557 |
| E-number FI | 4278037 |
| Warranty | 3 years |

Physical data

| | |
|-----------------------------|--------|
| Housing colour | Silver |
| Diffuser finish | Opal |
| Nominal Product Length (mm) | 2000 |
| Nominal Product Width (mm) | 30 |
| Nominal Product Height (mm) | 4.3 |
| Weight (kg) | 0.04 |

Packaging

| | |
|-----------------------|---------------|
| Single packaging type | Carton |
| Product EAN number | 5410288226200 |

Click Flat Diffusers

Cover C9 click 2m opal

0022620

| | |
|---------------------------------------|----------------|
| Packaging single length / height (cm) | 200.0 |
| Packaging single width (cm) | 3.0 |
| Packaging single depth (cm) | 2.0 |
| DUN14 (outer) | 05410288226200 |
| Units per outer package | 100 |
| Packaging outer length / height (cm) | 205.0 |
| Packaging outer width (cm) | 16.0 |
| Packaging outer depth (cm) | 16.0 |

TECHNICAL DRAWINGS

