

SylSafe IP65 LED

SYLSAFE IP65 LED M3 DALI/SELF TEST

9154052



Product features

- Maintained LED emergency luminaire with DALI/Self Test function (BSEN62034), IP65 polycarbonate body, 3 hour emergency duration, integral NiCD batteries (1 x 3.6V 1.8AH NiCD), 135lm, 7W (1.7W Charge).



PRODUCT OVERVIEW

Product name	SYLSAFE IP65 LED M3 DALI/SELF TEST
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
General application	Education, Hospitality, Office, Retail
Warranty	3 years
Fixture luminous flux (lm)	135
Colour temperature (K)	4000
Light colour	Neutral White
Electrical protection	Class II
Housing colour	White

DATA TABLE

General data

Product name	SYLSAFE IP65 LED M3 DALI/SELF TEST
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
General application	Education, Hospitality, Office, Retail
Warranty	3 years

Optical data

Fixture luminous flux (lm)	135
Colour temperature (K)	4000
Light colour	Neutral White
Adjustable chromaticity	N
Emergency duration (h)	3

Electrical data

Mains voltage (V)	220-240V
Electrical protection	Class II

SylSafe IP65 LED

SYLSAFE IP65 LED M3 DALI/SELF TEST

9154052

Physical data

Housing colour	White
Nominal Product Length (mm)	350
Nominal Product Width (mm)	120
Nominal Product Height (mm)	90
Weight (kg)	2.65

Packaging

Single packaging type	Carton
Packaging single length / height (cm)	38.0
Packaging single width (cm)	15.0
Packaging single depth (cm)	11.0
Units per outer package	1
Packaging outer length / height (cm)	38.0
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	11.0

TECHNICAL DRAWINGS

