



LED OFFICE LINE



	EAN	W	lm	K	⊖ (°C)	V~	mA	Hz	PF	👤
LED OFFICE LINE DIM 0.6 25 W / 840	4058075271500	25	2000	4000	-20...+40	220-240	111	50/60	>0.9	0.7 kg
LED OFFICE LINE DIM 1.2 50 W / 840	4058075271524	50	4000	4000	-20...+40	220-240	223	50/60	>0.9	1.2 kg
LED OFFICE LINE GRID DIM 0.6 25 W / 840	4058075271548	25	2000	4000	-20...+40	220-240	111	50/60	>0.9	0.7 kg
LED OFFICE LINE GRID DIM 1.2 50 W / 840	4058075271562	50	4000	4000	-20...+40	220-240	223	50/60	>0.9	1.4 kg



LED Office Line Grid DIM

1x








LED Office Line DIM




1x



H	mm
W	
H	
W	
L	
L x W x H [mm]	
GRID DIM 0.6 25W	595x134x46
GRID DIM 1.2 50W	1195x134x46
DIM 0.6 25W	595x134x46
DIM 1.2 50W	1195x134x46







C10567405
G11068586
11.02.2019



LEDVANCE GmbH
Steinerne Furt 62
86167 Augsburg, Germany
www.ledvance.com