

## 90° manual deburring tool, HSS, triple cutter

for universal use up to 1000 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For producing 90° counterbores and for deburring up to 1000 N/mm<sup>2</sup>.

### Execution:

- profile-ground triple-edge countersink with radial relief

### Advantage:

- radial relief ensures optimum chip breaking



<b>Art. no.</b>	<b>11511 220</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11511220
<b>Countersink angle</b>	90 Degree
<b>Cutting material</b>	HSS
<b>Surface</b>	Uncoated
<b>Number of cutting edges</b>	3 PCS
<b>Spot-facer diameter</b>	20.5 mm
<b>Gross Weight</b>	0.098 kg
<b>Product Group</b>	1EH

### EAN

405362503346 1