

## Electronic outside micrometer

QuantuMike IP65 Digimatic

Mitutoyo

### Application:

For measuring e.g. shaft diameters, external dimensions of workpieces etc.

### Execution:

- Carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- With ratchet barrel
- Digimatic

### Advantage:

- High battery life of approx. 2.4 years
- Faster measurement by using a larger thread pitch of 2 mm/rev

### Delivery:

Includes box, wrench, battery, setting standard (from 25 mm), up to 50-mm measuring range with factory test certificate



<b>Art. no.</b>	<b>32017 368</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	293-180-30
<b>Display</b>	Digital
<b>Min./max. length measuring range in inches</b>	0-1 in
<b>Digit increment</b>	0.00005 in
<b>Measuring surface diameter</b>	6.3 mm
<b>IP protection class</b>	IP 65
<b>Data transmission type</b>	DIGIMATIC
<b>Spindle clamping</b>	Yes
<b>Digit height</b>	7.5 mm
<b>Functions</b>	ABS function, Hold-function (AE lock), Origin (Dimension preset), Automatic switch-off
<b>Min./max. measurement force</b>	7-12 N
<b>Error limit</b>	0.00004 in
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	1,5 V SR44
<b>DIN</b>	863
<b>Bracket depth</b>	25 mm
<b>Measuring spindle increments</b>	2 mm
<b>Calibration Group</b>	D
<b>Gross Weight</b>	0.480 kg
<b>Product Group</b>	3MA

### EAN

4946368716640