

Table scales FKB



Application:

ideal for high-precision weighing in industrial environments

Execution:

- Count resolution 360,000
- Housing with robust aluminium high-pressure die casting tub, ensures stable positioning, protects the weighing technology and is hard-wearing in everyday use
- Especially practical: Thanks to large weighing ranges and compact dimensions, heavy loads can be weighed with high precision even in the smallest of spaces. Useful for determining the most minute weight differences such as gas consumed, abrasion of mechanical parts, rock samples, minerals, druse, silver etc.
- PRE-TARE function for manual prior deduction of a known container weight, useful for fill level checks
- Freely programmable weighing unit, e.g. display directly in wire length g/m, surface weight g/m² (paper, fabric, sheet metal etc.) or similar
- with large weighing tray

Delivery:

with power supply unit and work protection hood



Art. no.	49000 031
Brand	KERN
Manufacturer Part Number	FKB 8K0.05
Type description	FKB 8K0.05
Max. weight measuring range	8000 g
Digit increment, weight	0.05 g
Digit height	25 mm
Plate size	240 x 340 mm
Material of cover panel	Stainless steel
With unit counting	Yes
Min. item weight	500 mg
Reproducibility	0.05 g
Linearity	0.15 g
Settling time scale	3 s
Data transmission type	RS232
Display type	LCD
Housing dimensions (LxWxH)	350 x 390 x 120 mm
Gross Weight	7.400 kg
Product Group	447

EAN

4045761096042