

## Workbench with manual height adjustment

Solid beechwood 1500 mm, height-adjustable via crank handle

### Application:

For standing activities.

### Execution:

- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, central horizontal strut, with level compensation on all four feet
- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Bevel gears with hardened steel gear wheels
- Gear housing made of fibreglass-reinforced plastic
- Fully assembled incl. crank handle

### Advantage:

- The workbench can quickly and easily be adjusted to the desired working height
- For perfect ergonomics in the workplace
- When you buy this product, you plant a tree and also receive a tree certificate!



<b>Art. no.</b>	<b>50185 004</b>
<b>Worktop width</b>	1500 mm
<b>Levelling</b>	Yes
<b>Worktop height</b>	50 mm
<b>Adjustable in height</b>	Yes
<b>Material of frame</b>	Steel plate
<b>Worktop depth</b>	700 mm
<b>Max. height adjustment</b>	1040 mm
<b>Min. height adjustment</b>	740 mm
<b>Surface</b>	Powder-coated
<b>Load-carrying capacity</b>	800 kg
<b>Dynamic load-carrying capacity</b>	200 kg
<b>Type</b>	Height adjustable via hand crank
<b>Material of worktop</b>	Solid beech
<b>Product Group</b>	5BC

### EAN

4053625048854