

Wheeled workbenches, working height 950 mm

With 6 pull-out drawers on both sides

Application:

The mobile workstation with versatile options for use.

Execution:

- Sturdy and warp-free steel sheet structure, with push handle on the side of the housing
- 2 storage compartments, compartment height 370 mm with anti-roll-off edging, height 50 mm
- Side wall with square perforation grid, individual attachment options, e.g. with hooks for tools or other attachments such as can holders, paper roll holders, waste basket etc. for holding hooks and RasterPlan tool holders

Art. no.	50272 052
Number of drawers	6 PCS
Drawer front height	2 x 65 mm, 3 x 130 mm, 1 x 180 mm
Drawer width (inner dimension)	500 mm
Drawer depth (inner dimension)	400 mm
Load-carrying capacity per drawer	30 kg
Pullout type	Pull-out to both sides
With single pull-out safety brake	No
With single-locking drawers	No
Load-carrying capacity	450 kg
Dynamic load-carrying capacity	250 kg
Central locking	Yes
Lock type	Cylinder lock
Punched-hole, sidewall	Yes
Punched-hole	10 x 10 mm
With sliding handle	Yes
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
With wheel lock	No
Material of wheel	Solid rubber
Wheel diameter	100 mm
Material of worktop	Solid beech
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Surface	Powder-coated
Gross Weight	92.000 kg
Product Group	586

