

Drawer with full extension for drawer cabinet, system 700

Depth 600 mm

Application:

For individual fitting of the HK cabinet housing 700 B. The drawers can be installed in the housing in arbitrary sequence. The sum of the front heights must be the effective height of the housing.

Execution:

- Made of sheet steel metal with a reinforced, perforated bottom (25 mm hole grid)
- Run on Delrin rollers in rails which are suspended in the housing with plug caps
- Inner sides slotted all around, for attaching and fixing insert material such as compartment rails and dividers
- Equipped with aluminium handle strip, paper and cellon strips and lateral cover caps
- SOFT-CLOSE-AUTOMATIC for smooth and silent drawer closing, see no. 50392 005



Art. no.	50300 362
Brand	HK
Manufacturer Part Number	50300362
Drawer front height	60 mm
Drawer cabinet height	40 mm
Mount height	40 mm
Drawer width (inner dimension)	600 mm
Drawer depth (inner dimension)	600 mm
Drawer surface	0.36 m ²
Pullout type	Full extension
Load-carrying capacity	70 kg
Drawer with slots	Yes
Perforated drawer base	Yes
Material	Sheet steel
Colour of front	Gentian blue RAL 5010
Box colour	Light grey RAL 7035
Surface	Powder-coated
Gross Weight	0.001 kg
Product Group	5BB

EAN

4053625099658