

FireBird cordless blind rivet nut setting tool

FireBird Pro CAS model



Execution:

- electro-mechanical setting tool with automatic two-way drilling function
- cordless, with CAS sliding battery 18 V Li-Ion 2.0 Ah
- includes charger, nosepiece and M4, M5 and M6 threaded mandrels
- in L-Boxx
- for processing M3-M10 rivet nuts

Advantage:

- quick working speed while maintaining excellent performance
- high functional reliability thanks to simple drilling of blind rivet nuts and electronic control of the setting stroke
- balanced centre of gravity and ergonomic handle for extremely comfortable, fatigue-free work

Delivery:

replacement thread mandrels and nozzles available deliverable from stock - please request



Art. no.	53195 406
Model	FireBird Pro CAS
Battery included	Yes
Number of rechargeable batteries/batteries	1 PCS
Battery designation	Li-Ion battery type 5S1P
Weight of rechargeable battery/battery	0.435 kg
Rechargeable battery/battery capacity	2 Ah
Battery voltage	18 V
Type of rechargeable battery/battery	Li-Ion
Max. working stroke	10 mm
Gross weight	5.1 kg
Weight	2.3 kg
With rechargeable battery/battery	Operation with rechargeable battery
Rivet setting force	15000 N
Product Group	Prod. Gr. 5AL

EAN

4007081102513