

Kriechstrecken Kontakt-Kontakt [mm]: 1,2 mm

Luftstrecke Kontakt-Kontakt [mm]: 1,2 mm

Max. Strom bei 20°C: 2-A

Max. Widerstand: 20 mΩ

Max. Steck- und Ziehkräfte [N]: 90 N

Prüfspannung Ueff Kontakt-Kontakt [kV]: 1 kV

Prüfspannung Ueff Kontakt-Masse [kV]: 1,55 kV

Reihenanzuordnung: A; B; C

ZUSÄTZLICHE PRODUKTDDETAILS

Stecker / Buchse DIN Anschluss Form C.

Anforderungskategorie 2 nach EN 60603 (DIN 41642).

ZERTIFIZIERUNGEN



Nordamerika

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europa

Straubenhardt, Deutschland

+49.7082.794.0

Betschdorf, Frankreich

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, Volksrepublik

China

+86.532.8771.6101

Singapur

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, Indien

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.