


# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	C.K
<b>Product Range</b>	SDS Drills
<b>Catalogue number</b>	3120
<b>Date</b>	01/09/2014

<p><b>Range Description</b> A range of professional quality SDS Concrete drill bits</p>	
<p><b>Features</b></p> <ul style="list-style-type: none"> <li>• Tungsten carbide tipped with optimized geometry for drilling concrete and stone</li> <li>• Vacuum brazed tips for durability</li> <li>• Ground flutes designed for optimum debris removal</li> <li>• SDS-plus shank</li> </ul>	

Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
T3120 0511	SDS Drill Bit 5x48x110mm	5013969644517	82075030	50
T3120 0516	SDS Drill Bit 5x90x160mm	5013969644524	82075030	50
T3120 05511	SDS Drill Bit 5.5x48x110mm	5013969644531	82075030	50
T3120 05516	SDS Drill Bit 5.5x90x160mm	5013969644548	82075030	50
T3120 0611	SDS Drill Bit 6x50x110mm	5013969644555	82075030	50
T3120 0616	SDS Drill Bit 6x90x160mm	5013969644562	82075030	50
T3120 0621	SDS Drill Bit 6x140x210mm	5013969644579	82075030	50
T3120 06516	SDS Drill Bit 6.5x90x160mm	5013969644586	82075030	50
T3120 0716	SDS Drill Bit 7x90x160mm	5013969644593	82075030	50
T3120 0816	SDS Drill Bit 8x90x160mm	5013969644609	82075030	50
T3120 0821	SDS Drill Bit 8x140x210mm	5013969644616	82075030	50
T3120 0826	SDS Drill Bit 8x185x260mm	5013969644623	82075030	50
T3120 0845	SDS Drill Bit 8x350x450mm	5013969644630	82075030	50
T3120 1016	SDS Drill Bit 10x90x160mm	5013969644647	82075030	50

T3120 1021	SDS Drill Bit 10x140x210mm	5013969644654	82075030	50
T3120 1026	SDS Drill Bit 10x185x260mm	5013969644661	82075030	50
T3120 1045	SDS Drill Bit 10x350x450mm	5013969644678	82075030	50
T3120 12100	SDS Drill Bit 12x950x1000	5013969644685	82075030	5
T3120 1215	SDS Drill Bit 12x90x160mm	5013969644692	82075030	50
T3120 1221	SDS Drill Bit 12x140x200mm	5013969644708	82075030	50
T3120 1225	SDS Drill Bit 12x180x260mm	5013969644715	82075030	50
T3120 1245	SDS Drill Bit 12x350x450mm	5013969644722	82075030	50
T3120 1425	SDS Drill Bit 14x180x260mm	5013969644739	82075030	50
T3120 1445	SDS Drill Bit 14x350x450mm	5013969644746	82075030	50
T3120 16100	SDS Drill Bit 16x950x1000	5013969644753	82075030	5
T3120 1630	SDS Drill Bit 16x250x310mm	5013969644760	82075030	50
T3120 1645	SDS Drill Bit 16x350x450mm	5013969644777	82075030	40
T3120 1830	SDS Drill Bit 18x250x310mm	5013969644784	82075030	50
T3120 1845	SDS Drill Bit 18x350x450mm	5013969644791	82075030	40
T3120 20100	SDS Drill Bit 20x950x1000	5013969644807	82075030	5
T3120 2030	SDS Drill Bit 20x250x310mm	5013969644814	82075030	50
T3120 2045	SDS Drill Bit 20x350x450mm	5013969644821	82075030	30
T3120 25100	SDS Drill Bit 25x950x1000	5013969644838	82075030	5
T3120 2545	SDS Drill Bit 25x350x450mm	5013969644845	82075030	20
T3121	SDS Drill Bit Set of 7	5013969644852	82075030	20

Technical product information	
Standards compliance	
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Drills are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	China

## Dimensional Details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3120 0511	110	5	10	31.80	171.5	36	12.7	36.00
T3120 0516	160	5	10	37.80	221.5	36	12.7	42.00
T3120 05511	110	5.5	10	43.80	171.5	36	12.7	48.00
T3120 05516	160	5.5	10	39.80	221.5	36	12.7	44.00
T3120 0611	110	6	10	36.80	171.5	36	12.7	41.00
T3120 0616	160	6	10	23.80	221.5	36	12.7	28.00
T3120 0621	210	6	10	49.80	271.5	36	12.7	54.00
T3120 06516	160	6.5	10	46.80	221.5	36	12.7	51.00
T3120 0716	160	7	10	46.80	221.5	36	12.7	51.00
T3120 0816	160	8	10	52.80	221.5	36	12.7	57.00
T3120 0821	210	8	10	65.80	271.5	36	12.7	70.00
T3120 0826	260	8	10	70.80	321.5	36	12.7	75.00
T3120 0845	450	8	10	95.80	511.5	36	12.7	100.00
T3120 1016	160	10	10	66.80	221.5	36	12.7	71.00
T3120 1021	210	10	10	82.80	271.5	36	12.7	87.00
T3120 1026	260	10	10	101.80	321.5	36	12.7	106.00
T3120 1045	450	10	10	172.80	511.5	36	12.7	177.00
T3120 12100	1000	12	12	395.80	1061.5	36	12.7	400.00
T3120 1215	160	12	12	76.80	221.5	36	12.7	81.00
T3120 1221	210	12	12	95.80	271.5	36	12.7	100.00
T3120 1225	260	12	12	119.80	321.5	36	12.7	124.00
T3120 1245	450	12	12	183.80	511.5	36	12.7	188.00
T3120 1425	260	14	14	151.80	321.5	36	14	156.00
T3120 1445	450	14	14	260.80	511.5	36	14	265.00
T3120 16100	1000	16	16	695.80	1061.5	36	16	700.00
T3120 1630	300	16	16	219.80	361.5	36	16	224.00
T3120 1645	450	16	16	295.80	511.5	36	16	300.00
T3120 1830	300	18	18	270.80	361.5	36	18	275.00
T3120 1845	450	18	18	316.80	511.5	36	18	321.00
T3120 20100	1000	20	20	995.80	1061.5	36	20	1000.00
T3120 2030	310	20	20	272.80	371.5	36	20	277.00
T3120 2045	450	20	20	395.80	511.5	36	20	400.00
T3120 25100	1000	25	25	1495.80	1061.5	36	25	1500.00
T3120 2545	450	25	25	805.80	511.5	36	25	810.00

T3121	various	various	various	329.80	184	108	27	615.90
-------	---------	---------	---------	--------	-----	-----	----	--------

Shelf box (secondary packaging)					Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3120 0511	262	131	89	1878.00		
T3120 0516	262	131	89	2178.00		
T3120 05511	262	131	89	2478.00		
T3120 05516	262	131	89	2278.00		
T3120 0611	262	131	89	2128.00		
T3120 0616	262	131	89	1478.00		
T3120 0621	325	136	91	2810.00		
T3120 06516	262	131	89	2628.00		
T3120 0716	262	131	89	2628.00		
T3120 0816	262	131	89	2928.00		
T3120 0821	325	136	91	3610.00		
T3120 0826	325	136	91	3860.00		
T3120 0845	550	120	100	5257.00		
T3120 1016	325	136	91	3660.00		
T3120 1021	325	136	91	4460.00		
T3120 1026	325	136	91	5410.00		
T3120 1045	550	120	100	9107.00		
T3120 12100	40	1000	120	2276.00		
T3120 1215	325	136	91	4160.00		
T3120 1221	325	136	91	5110.00		
T3120 1225	325	136	91	6310.00		
T3120 1245	550	120	100	9657.00		
T3120 1425	325	136	91	7910.00		
T3120 1445	550	120	100	13507.00		
T3120 16100	40	1000	120	3776.00		
T3120 1630	410	315	130	11450.00		
T3120 1645	550	120	100	12257.00		
T3120 1830	410	315	130	14000.00		

T3120 1845	550	120	100	13097.00		
T3120 20100	40	1000	120	5276.00		
T3120 2030	410	315	130	14100.00		
T3120 2045	550	120	100	12257.00		
T3120 25100	40	1000	120	7776.00		
T3120 2545	550	120	100	16457.00		
T3121	400	300	120	12706.60		

### Packaging Waste Details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3120 0511	4.2	1	0	0	210	50	0	0
T3120 0516	4.2	1	0	0	210	50	0	0
T3120 05511	4.2	1	0	0	210	50	0	0
T3120 05516	4.2	1	0	0	210	50	0	0
T3120 0611	4.2	1	0	0	210	50	0	0
T3120 0616	4.2	1	0	0	210	50	0	0
T3120 0621	4.2	1	0	0	210	50	0	0
T3120 06516	4.2	1	0	0	210	50	0	0
T3120 0716	4.2	1	0	0	210	50	0	0
T3120 0816	4.2	1	0	0	210	50	0	0
T3120 0821	4.2	1	0	0	210	50	0	0
T3120 0826	4.2	1	0	0	210	50	0	0
T3120 0845	4.2	1	0	0	210	50	0	0
T3120 1016	4.2	1	0	0	210	50	0	0
T3120 1021	4.2	1	0	0	210	50	0	0
T3120 1026	4.2	1	0	0	210	50	0	0
T3120 1045	4.2	1	0	0	210	50	0	0
T3120 12100	4.2	1	0	0	21	5	0	0
T3120 1215	4.2	1	0	0	210	50	0	0
T3120 1221	4.2	1	0	0	210	50	0	0
T3120 1225	4.2	1	0	0	210	50	0	0

T3120 1245	4.2	1	0	0	210	50	0	0
T3120 1425	4.2	1	0	0	210	50	0	0
T3120 1445	4.2	1	0	0	210	50	0	0
T3120 16100	4.2	1	0	0	21	5	0	0
T3120 1630	4.2	1	0	0	210	50	0	0
T3120 1645	4.2	1	0	0	168	40	0	0
T3120 1830	4.2	1	0	0	210	50	0	0
T3120 1845	4.2	1	0	0	168	40	0	0
T3120 20100	4.2	1	0	0	21	5	0	0
T3120 2030	4.2	1	0	0	210	50	0	0
T3120 2045	4.2	1	0	0	126	30	0	0
T3120 25100	4.2	1	0	0	21	5	0	0
T3120 2545	4.2	1	0	0	84	20	0	0
T3121	2.6	1	0	0	52	20	0	0