

## Han 10M Base Panel 2 Levers



|                    |   |
|--------------------|---|
| Part number        | 09 37 010 0301  |
| Specification      | Han 10M Base Panel 2 Levers   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09370100301">https://b2b.harting.com/09370100301</a> |

### Identification

|                          |                           |
|--------------------------|---------------------------|
| Category                 | Hoods/Housings            |
| Series of hoods/housings | Han <sup>®</sup> M        |
| Type of hood/housing     | Bulkhead mounted housings |
| Type                     | Low construction          |

### Version

|                      |                                       |
|----------------------|---------------------------------------|
| Locking type         | Double locking lever                  |
| Size                 | 10 B                                  |
| Field of application | Hoods/housings for rough environments |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|                             |                      |
|-----------------------------|----------------------|
| Material (hood/housing)     | Aluminium die-cast   |
| Surface (hood/housing)      | Powder-coated        |
| Colour (hood/housing)       | RAL 9005 (jet black) |
| Material (seal)             | FPM                  |
| Material (locking)          | Stainless steel      |
| RoHS                        | compliant            |
| ELV status                  | compliant            |
| China RoHS                  | e                    |
| REACH Annex XVII substances | No                   |
| REACH ANNEX XIV substances  | No                   |



Pushing Performance

## Material properties

|                       |    |
|-----------------------|----|
| REACH SVHC substances | No |
|-----------------------|----|

## Specifications and approvals

|           |  |
|-----------|--|
| Approvals | DNV GL   |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 134.9 g  |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |